

Venez découvrir à Ternat notre showroom flambant neuf et laissez-vous convaincre de la qualité et du design Falmecc par un expert **falmecc**

Les jours ouvrés de 10:00 à 12:00 heures et de 14:00 à 17:00 heures.
Fermé le week-end et les jours fériés.

Les modèles suivants sont exposés dans notre show-room



FA AURA120WGW



FA DOWN90DB
(Black, 90 cm)



FA ECLISSE120PW



FA FLIP85WSW
(White)



FA GHOST60VWV
(White)



FA GRINC70C
(Inox, 70cm)



FA GRINCMUR70CW
(Glass White, 70 cm)



FA LAGU60W (Body)
FA-LAGUPW60GW (Glass)
(Glass White, 60 cm, Wall)



FA LUCE90WB
(Black, Wall)



FA LUM90WGNRS
(Inox, 90 cm, Wall)



FA LUMEN175E



FA LUX90WI
(90 cm, Wall)



FA MARE66EGWion (White, Island)
FA MARE66EGBion (Black, Island)



FA MOVE60TB
(Black, 60 cm, Wall)



FA NUVO140P
(Inox, 140 cm)



FA PIANODOUBD



FA PLANE90VWV
(White, 90 cm, Wall)
Also exposed in Inox



FA BODY67WQ (Body Square)
FA-PLAT67WQ (Glass)
(67 cm, Wall)



FA BODY67WR (Body Round)
FA-PHARO67WR (Glass)
(67 cm, Wall)



FA POLAR35RWR
(White, Wall)



FA PRISMA85VWV
(Black, 85 cm)



FA RIALTOT55WI



FA RUBIK42EGBion
(Black, Island)



FA SPRIN80EGWion
(White, Island)




FA STELL120IP
(Inox, 120 cm)



FA STREAM90V



FA TAB60WGREY
(Grey, 60 cm, Wall)



FA TWIS45ETITION
(Titanium, Island)



FA VIRGO60V
(60 cm)



FA SPAZI180EBCIR
(Island, 180 cm)



FA HOBPIANO59RC (with RC)
FA HOBPIANO59 (without RC)



FA HOBPIANO78 (without RC)

falmec



FA DAMA60EWCIR
(White, 60 cm, Island)



FA SOPH45EKCIR
(Copper, 45 cm, Island)



FA SOFFIO58EWCIR
(White, 58 cm, Island)



FA LOOP74EGUNCIR
(Gunmetal, 74 cm, Island)



FA OCEAN180EGio
(White, 180 cm, Inox)

falmec